

SONY®

3-CCD Color Video Camera

DXC-C33/C33P



Ideal for use in space-limited locations, the DXC-C33/C33P incorporates one of the smallest/lightest camera head unit featuring three 1/3 type CCDs. In spite of its compact (32 (W) x 38 (H) x 40 (D) mm, 1 5/16 x 1 1/2 x 1 5/8 inches) and lightweight (48 g, 1.7 oz) camera head unit, this model inherits superb picture quality of the DXC Series. Its horizontal resolution is 850 TV lines and the minimum illumination is 2000 lux at F8. Also, various features such as DynaLatitude™, Partial Enhance are provided to this model. First for the DXC Series and also first for 3-CDD small head cameras, the DXC-C33/C33P is equipped with a DV output terminal. Thanks to the DV output terminal, video signals can be recorded to i.LINK™ interface-equipped VTR with no quality deterioration.


With the excellent features and medical approval, the DXC-C33/C33P is the right choice for medical fields, and also for demanding applications such as research and industrial fields.



Industrial inspection



Microscopy



Sports shooting



Features

Small camera head

The DXC-C33/C33P can be installed in space-limited locations. The size of the camera head unit (CHU) is one of the smallest of all the 1/3 type 3-CCD cameras.

High picture quality

The DXC-C33/C33P can clearly capture detailed images of objects. Adoption of three 1/3 type CCDs allows the camera to realize 2000 lux at F8, S/N ratio of 62 dB (NTSC) or 61 dB (PAL) and achieve a horizontal resolution of 850 TV lines.



800 TV lines picture



850 TV lines picture

(Simulated picture)

i.LINK DV out

DV output terminal allows image recording into i.LINK interface-equipped VTR with no quality deterioration.

This feature is first introduced to small head 3CCD cameras.



DSR-70A/70AP and DXC-C33/C33P

* i.LINK stands for IEEE-1394-1995 standards and their revisions.

 is the logo for products that implement i.LINK.

Note: Sony VAIO computers are checked with Sony DV products, but not with DVCAM, concerning the i.LINK interconnection. Some VAIO application software may not work with DVCAM.

10-bit DSP

The DXC-C33/C33P can capture superior pictures by adopting full Digital Signal Processing (DSP) of 10 bits.

DynaLatitude

This function automatically adjusts contrast corresponding to the brightness signal level of the entire image. Clear images can be captured if both bright and dark areas exist within an image.



OFF

ON

(Simulated picture)

Frame memory

Built-in frame memory can provide a freeze image and a remarkably enhanced image in sensitivity by long-time exposure function. Images captured by long-time exposure function can be output continuously.



Gain: 18 dB



Long Exp: 32 frames

Partial Enhance

This function allows a particular color to be selected, and its hue, saturation and detail altered. In addition, the detail produced by the high resolution of the camera can be softened or emphasized in certain parts of the image by the Partial Enhance function.



OFF

ON


User-friendly control panel

The front panel is easy to use with smartly arranged knob switches and good-sized switches.



Two AE areas preset

AE (Automatic Exposure) function is very useful to determine the best area for incoming light metering. Users can select and set up two of the six different AE modes and can easily switch them at front panel.



Multi

Mid

Slit

Large

Spot

Manual

RS-232C interface

Easy control and operation of the camera by an external computer is possible.

External synchronization (HD/VD, VBS)

External, synchronization allows for multiple camera operation.

3-CCD Color Video Camera
DXC-C33/C33P

Optional Accessories



VCL-08WM
VCL-16WM
VCL-25WM



DVCAM™ Series
(DSR-20MD/20MDP)



RM-C950
Remote Control Unit



CCMC-20P05/20P10/20P30
20-pin Multi Cable (5/10/30 m)



VMC-IL4615/IL4635
i.LINK Cable (1.5/3.5 m)




CCXC-9DB/9DD
9-pin D-sub Cable



CCMC-9DS
9-pin D-sub Cable

Typical System



Specifications

Pick-up device	1/3 type IT (Interline Transfer) CCD (x3)	Detail frequency	HIGH/MID/LOW selectable
Effective picture elements	NTSC: 768 (H) x 494 (V) PAL: 752 (H) x 582 (V)	Linear matrix	ALL/TARGET/OFF
Sensing area	4.8 (H) x 3.6 (V) mm	Linear matrix mode	STANDARD/R Enhance/G Enhance/B Enhance/Manual selectable
Scanning system	NTSC: 2:1 interlaced, 525 lines PAL: 2:1 interlaced, 625 lines	Partial enhance	ALL/IN/OUT selectable
Horizontal frequency	NTSC: 15.734 kHz PAL: 15.625 kHz	CCD integration mode	FIELD/FRAME selectable
Vertical frequency	NTSC: 59.94 Hz PAL: 50 Hz	Shading compensation	OFF/ON (Manual control)
Sync system	Internal or external with VBS or HD/VD	Trigger polarity	Positive edge trigger/Negative edge trigger selectable
Phase control	H/SC phase control	Baud rate	19200/9600/4800/2400/1200 selectable
Horizontal resolution	850 TV lines	Sync	RGB/G/OFF selectable
Lens mount	C mount	Strobe	Slave
Flange back	17.526 mm in air	User file	A/B switchable (Two pattern memories)
Sensitivity	F8.0 at 2000 lux (3200 K)	Scene file	STANDARD/MICROSCOPE/ FULL AUTO/STROBE/FILE A or B
Minimum illumination	4 lux (F2, GAIN: HYPER)	Output signal	i.LINK (DV): IEEE1394 Based VBS: 1.0 Vp-p, 75 Ω, sync negative RGB: 0.7 Vp-p, 75 Ω, sync switchable SYNC: 2 Vp-p, 75 Ω Y: 1.0 Vp-p, 75 Ω C: NTSC 0.286 Vp-p, 75 Ω, without sync PAL 0.3 Vp-p, 75 Ω, without sync
S/N ratio	NTSC: 62 dB (Typical) PAL: 61 dB (Typical)	Operating temperature	-5 to 45°C (23 to 113°F)
Gain	STEP/AGC/HYPER selectable STEP: 0 to 24 dB by 1 dB step AGC: 0 to 24 dB (Limit value: 6 dB, 12 dB, 18 dB, 24 dB selectable) HYPER: 30 dB	Storage temperature	-20 to 60°C (-4 to 140°F)
Electronic shutter	8.0 to 1/100,000 s	Power supply	100 to 240 V AC, 50/60 Hz
Lens	Manual Iris	Power consumption	Max. 18 W
AE area	Multi/Large/Medium/Spot/Slit/ Manual selectable	Dimensions	CHU: 32 (W) x 38 (H) x 40 (D) mm (1 5/16 x 1 1/2 x 1 5/8 inches) CCU: 200 (W) x 88 (H) x 242 (D) mm (7 7/8 x 3 1/2 x 9 5/8 inches)
AE level	Variable	Mass	CHU: 48 g (1.7 oz) CCU: 2.5 kg (5 lb 8 oz)
AE speed	Fast/Mid/Slow selectable	Connectors	DV OUT (6-pin jack) RGB/SYNC (9-pin D-sub) VIDEO OUT (BNC) S-VIDEO (4-pin mini DIN) FS/TRIG IN (Stereo Mini jack) REMOTE (8-pin mini DIN) AC Inlet Camera (20-pin)
AE detect	Average/Peak selectable	Supplied accessories	Tripod adaptor AC power cable Lens cap Panel sheet for RM-C950 Operation instruction manual
Contrast effect	Manual/DynaLatitude/DCC+ selectable		
Knee point	High/Normal/Low selectable (Contrast Effect: Manual)		
Black stretch	Variable (Contrast Effect: Manual)		
Gamma	ON/OFF (Variable at ON)		
Pedestal	Master and R/B Manual adjustable		
Black balance	ABB		
White balance	AWB/ATW NORMAL/ATW WIDE/ MANUAL/3200 K/5600 K selectable AWB or ATW R/B Paint, MANUAL R/B Gain		
ATW area	NORMAL/MANU selectable		
ATW speed	FAST/NORMAL/SLOW selectable		
Detail level	ALL/TARGET/OFF (Variable at ALL or TARGET)		

Pin Assignment


9-pin D-sub connector



Menu	D-sub VIDEO: VBS D-sub SYNC: C.SYNC	D-sub VIDEO: VBS D-sub SYNC: WEN	D-sub VIDEO: Y/C D-sub SYNC: C.SYNC	D-sub VIDEO: Y/C D-sub SYNC: WEN
1	VBS OUT (G)	VBS OUT (G)	Y/C OUT (G)	Y/C OUT (G)
2	RGB OUT (G)	RGB OUT (G)	RGB OUT (G)	RGB OUT (G)
3	R OUT (X)	R OUT (X)	R OUT (X)	R OUT (X)
4	G OUT (X)	G OUT (X)	G OUT (X)	G OUT (X)
5	B OUT (X)	B OUT (X)	B OUT (X)	B OUT (X)
6	VBS OUT (X)	VBS OUT (X)	Y OUT (X)	Y OUT (X)
7	C.SYNC OUT (X)	WEN OUT (X)	C.SYNC OUT (X)	WEN OUT (X)
8	C.SYNC OUT (G)	WEN OUT (G)	C.SYNC OUT (G)	WEN OUT (G)
9	(X)	(X)	C OUT (X)	C OUT (X)


MINI DIN 8-pin connector

1	INTER CONNECT
2	INTER CONNECT
3	DATA OUT
4	DC OUT (G)
5	DATA IN
6	NC
7	DC OUT (+)
8	NC




Dimensions

DXC-C33/C33P CCU



DXC-C33/C33P CHU



Unit: mm

Distributed by

©2001 Sony Corporation. All rights reserved.
 Reproduction in whole or in part without written permission is prohibited.
 Features and specifications are subject to change without notice.
 All non-metric weights and measures are approximate.
 DynaLatitude, i.LINK and DVCAM are trademarks of Sony Corporation.
 Sony is a registered trademark of Sony Corporation.